

Partner: Clearone
Model: ConvergePro2
Device Type: Digital Signal Processor



GENERAL INFORMATION

SIMPLWINDOWS NAME:	Clearone ConvergePro2 GainMute Control v1.4
CATEGORY:	Mixer
VERSION:	1.4
SUMMARY:	<p>This module controls all Gain/Mute points in the Clearone ConvergePro2 where the BLOCK_NAME is "LEVEL" and the PARAMETER_NAME is "GAIN" or "GAIN_FINE". The control point must also have a PARAMETER_NAME of "MUTE". This module also uses MAX_GAIN and MIN_GAIN to automatically set the limits.</p> <p><i>If the control point that you need to control, does not meet with these requirements, use the "Clearone ConvergePro2 EP Generic Control v1.4" control module.</i></p>
GENERAL NOTES:	
CRESTRON HARDWARE REQUIRED:	3-series processor only
SETUP OF CRESTRON HARDWARE:	This module requires the "Clearone ConvergePro2 Command Processor IP v1.4" or the "Clearone ConvergePro2 Command Processor RS232 v1.4" modules in order to operate. Please read the help files associated with these modules.
VENDOR FIRMWARE:	v5.0.35.0

Partner: Clearone
Model: ConvergePro2
Device Type: Digital Signal Processor

**PARAMETER:**

Command_Processor_ID	Setting to indicate the ID for the command processor that this module will register itself with.
Channel_Name	You must use the DSP Control Points "Named" Value vs the EPT/EPN values. Correct Example: "Mic-01" or "VoIP_1_Rx".
Gain_Type	You must pick "GAIN_FINE" for all Mic control points, and "GAIN" for all the rest.
Step_Value	Up/Down Ramp db value selection.

Partner: Clearone
Model: ConvergePro2
Device Type: Digital Signal Processor



CONTROL:

Poll	D	Pulse to poll for the current value.
Gain_Up, Gain_Down	D	Press and hold to adjust the gain level. Use the parameter "Step_Value". <i>Increasing the value of the Step_Value will speed up how long it takes to get at the limits.</i>
GainDB_Value	A	Sets the value to be set using Set_GainDB . If the digital signal Set_GainDB is high when this value changes, the module will automatically send the new value. The value will be validated prior to sending to insure this value falls in the correct range. This is a signed dB level . Valid ranges are the Max Level or Min Level settings set inside your Clearone ConvergePro2 programming. Note: A debounce value of 300ms has been added preventing this value to be reset to quickly, thus safe guarding communication queues. DO NOT BYPASS. Note: this input is not designed to be used with a Ramp symbol in SIMPL Windows. It is only designed to be used for preset levels and SMART Graphic Sliders.
Set_GainDB	D	Pulse to send the gain entered in the GainDB_Value input. This will allow preset values to be sent to the Clearone ConvergePro2. <i>When using SMART Graphic Sliders, tie the digital press join to this signal.</i>
GainPrecent_Value	A	Sets the value to be set using Set_GainPercent . If the digital signal Set_GainPercent is high when this value changes, the module will automatically send the new value. The value will be validated prior to sending to insure this value falls in the correct range. This is an unsigned level . Note: A debounce value of 300ms has been added preventing this value to be reset to quickly, thus safe guarding communication queues. DO NOT BYPASS. Note: this input is not designed to be used with a Ramp symbol in SIMPL Windows. It is only designed to be used for preset levels and SMART Graphic Sliders. Value Range: 0d-65535d
Set_GainPercent	D	Pulse to send the gain entered in the GainPrecent_Value input. This will allow preset values to be sent to the Clearone. <i>When using SMART Graphic Sliders, tie the digital press join to this signal.</i>
Mute_On	D	Pulse to turn on Mute.
Mute_Off	D	Pulse to turn off Mute.
Mute_Toggle	D	Pulse to toggle Mute.

Partner: Clearone
Model: ConvergePro2
Device Type: Digital Signal Processor

**FEEDBACK:**

Is_Initialized	D	Signal is high to indicate the module has successfully received all required responses from its initializing queries.
GainDB_FB	A	Analog gain level value. This is the signed dB level.
GainPercent_FB	A	Analog volume level value. This is the scaled unsigned level based on the Min/Max range for the level. Value Range: 0d-65535d
Mute_On_FB	D	Mute On Status
Mute_Off_FB	D	Mute Off Status

Partner: Clearone
Model: ConvergePro2
Device Type: Digital Signal Processor

**TESTING:**

OPS USED FOR TESTING:	CP3: v1.601.3857.30174
SIMPL WINDOWS USED FOR TESTING:	4.11.06
CRES DB USED FOR TESTING:	81.05.001.00
DEVICE DATABASE:	107.00.001.00
SYMBOL LIBRARY USED FOR TESTING:	1091
SAMPLE PROGRAM:	Clearone ConvergePro2 v1.4 IP Demo Clearone ConvergePro2 v1.4 RS232 Demo
REVISION HISTORY:	v1.0 – Initial Release v1.1 – No revisions have been made to this module. v1.2 – No revisions have been made to this module. v1.4 – No revisions have been made to this module.