

Partner: Lutron
Model: HomeWorks QSX
Device Type: Lighting



GENERAL INFORMATION

SIMPLWINDOWS NAME:	Lutron HomeWorks QSX Shade Group Control v1.2
CATEGORY:	Lighting, HVAC, Shades
VERSION:	1.2
SUMMARY:	This module provides monitor and control capability for a Shade Group component as part of a Lutron HomeWorks QSX solution.
GENERAL NOTES:	This module interacts with a single Shade Group component, if multiple shade group components need to be managed, one module can be added for each component in the solution. This module requires one instance of the Lutron HomeWorks QSX Command Processor module to register with.
CRESTRON HARDWARE REQUIRED:	Crestron 3-Series processor. Crestron 4-Series processor (Firmware Version 2.5000 or later).
SETUP OF CRESTRON HARDWARE:	Crestron CP3 Crestron MC4
VENDOR FIRMWARE:	22.02.16f000
VENDOR SETUP:	Lutron HomeWorks QSX Processor

Partner: Lutron
Model: HomeWorks QSX
Device Type: Lighting

**PARAMETER:****Command_Processor_ID**

Setting indicates the identifier of the Command Processor module this module registers with. A single program can contain multiple shade modules where multiple Lutron processors are involved.

Shade_Mode

Setting indicates mode of operation of the shade group component, either lift, lift and tilt, or lift and tilt when closed.

NOTE: When 'Lift & Tilt When Closed' is selected, the tilt functionality is disabled unless the 'Lift Level of the shade is at 0'.

Zone_Href_ID

Setting indicates the reference identifier for the zone this shade control belongs to.

Example: for zone href: /Zone/1399, enter the value 1399 in the parameter field.

Partner: Lutron
Model: HomeWorks QSX
Device Type: Lighting

**CONTROL:**

Lift_Raise	D	Pulse to incrementally raise the shade position or latch high to continuously raise the shade position until the signal is latched low or the shade has reached its limit.
Lift_Lower	D	Pulse to incrementally lower the shade position or latch high to continuously lower the shade position until the signal is latched low or the shade has reached its limit.
Set_Lift_Level	D	Pulse to set the discrete value of the lift position specified by the Lift_Level analog input signal. <i>For slider operations, use a press join to drive this signal high. When this is high, the corresponding analog value will be sent automatically on change. Using a '1' on a 'set' signal is discouraged and will have negative effect.</i>
Lift_Level	A	Integer value specifies the lift position to set as a percentage. Range is 0 to 65535.
Tilt_Raise	D	Pulse to incrementally increase the tilt position or latch high to continuously increase the tilt position until the signal is latched low or the shade has reached its limit.
Tilt_Lower	D	Pulse to incrementally decrease the tilt position or latch high to continuously decrease the tilt position until the signal is latched low or the shade has reached its limit.
Set_Tilt_Level	D	Pulse to set the discrete value of the tilt position specified by the Tilt_Level analog input signal. <i>For slider operations, use a press join to drive this signal high. When this is high, the corresponding analog value will be sent automatically on change. Using a '1' on a 'set' signal is discouraged and will have negative effect.</i>
Tilt_Level	A	Integer value specifies the tilt position to set as a percentage. Range is 0 to 65535.

Partner: Lutron
Model: HomeWorks QSX
Device Type: Lighting

**FEEDBACK:**

Is_Initialized	D	High indicates the module is initialized. The module is initialized when all component state information has been updated in the module to reflect current component state.
Lift_Level_Fb	A	Integer value indicates the current lift position as a percentage from 0 to 65535.
Tilt_Level_Fb	A	Integer value indicates the current tilt position as a percentage from 0 to 65535.

Partner: Lutron
Model: HomeWorks QSX
Device Type: Lighting

**TESTING:**

OPS USED FOR TESTING:	CP3 1.8001.4788.20471 MC4 2.7000.00052
SIMPL WINDOWS USED FOR TESTING:	4.20
CRES DB USED FOR TESTING:	211.0500.001.00
DEVICE DATABASE:	200.17500.001.00
SYMBOL LIBRARY USED FOR TESTING:	1164
SAMPLE PROGRAM:	Lutron HomeWorks QSX v1.2 Demo IP.smw
REVISION HISTORY:	v1.0 – Initial Release v1.1 – Added shade group parameter: Lift and Tilt When Closed v1.2 – No changes have been made